



1112 E Washington Ave. Santa Ana, Ca. 92701  
(714) 547-5477

## ***CLEANING and HANDLING INSTRUCTIONS FOR Noxtat Edge Coat:***

*For convenience, we offer our customers NOXTAT EDGE COAT, which comes in 2 oz. containers. Noxtat Edge Coat is a solvent that the customer can apply to the uncoated edges of sheets or manufactured parts, to maintain continuity of electro static dissipation. **Isobutanol, has a pungent odor that should be avoided as much as possible. Avoid spills, and keep area well ventilated. Keep container tightly closed when not in use.***

**DIRECTIONS:** *To apply NOXTAT EDGE COAT, first shake bottle thoroughly to keep uniform. With a brush or Q-tip, apply solvent to the edges of your material or parts to be coated. Solvent will air dry in several hours. Allow to completely dry before use. **To clean excess edge coat solvent, use Isopropyl Alcohol or rubbing alcohol.***

**CLEANING INSTRUCTIONS:** *To clean NOXTAT SD sheet or part after handling, use a standard clean room cleaning product. The Noxtat coated sheet or part can also be cleaned with any commercial window cleaner without damage.*

**NOTICE:** ***Whenever handling chemicals, use in accordance with good industrial hygiene and safety practices. Use rubber gloves, safety glasses and a properly fitting respirator (NIOSH/MSHA approved) during exposure. Refer to our MSDS, Material Safety Data Sheet.***

**For further information please call or email us at:  
(714) 547-5477 or [info@noxtat.com](mailto:info@noxtat.com)**